



System Description Sheet No. 311

Epoxy Polymer Trowel Floor Overlay System

Description

CrownStone TD, System No. 311 is a 100% Solids, 100% reactive, moisture-insensitive non shrink, 3 component, Epoxy Polymer Mortar formulated to be hand or power-troweled applied at a typical thickness of 3/16 - 1/4 in. Crown TD cures to very tough and durable, dense mortar for applications demanding a superior abrasion wear and impact resistance.

Use

- Shallow, Partial & Full Depth Patching.
- · Great restoration system to resurface and waterproof
- For heavy-duty protected overlay floor
- To resurface old worn concrete
- For pitching or to pitch concrete areas for discharging to drains

Advantages

- Complies with USDA, FDA, OSHA, ADA
- No VOCs 100% solids formula
- Nearly no odor during application
- Non-Shrink
- Moisture insensitive formula
- Cures down to 50°F; lower curing temperature products are available
- Fast Cure available
- Very dense, less than 2% voids
- Excellent Strength Properties
- High Vibration Resistance
- Easy to hand and power trowel

Typical Coverage

Use product 310 primer to wet out surface, priming substrate.

CS 65 kit 39-43 Sq ft. at 1/4" and 43-48 sq ft. at 3/16"

Mix Ratio

Typical mix ratio for hand trowel or power trowel is 1:7-1:8 resin to Crown Trowel Blend Sand. Mix ratio depends on environmental conditions. Trowel Sand provided by Crown Polymers Corp.

Typical Data for Crown TD

(Mix ratio 1:7 Prod. No. 311 to aggregate)

Compressive Strengt	hs		
ASTM C579, 7 day full	cure,		11,500 psi
Hardness			
ASTM D2240, Neat Ep	oxy, 7 day full	cure,	Shore D 80
Indentation (Load)			
MIL-D-3134, Para. 4.7.	.4.2.1, 7 day c	ure	
Method: 1 in. diameter steel ram steadily applies a load of 2,000 lbs.			
for 30 min. on the test	specimen that	is placed on conc	rete.
Value		0.004 in.	indentation
Indentation (Impact)			
MIL-D-3134, Para. 4.7.	.3, 7 day cure,		
Method: 2 lb. steel ball	is dropped tw	ice from an 8 ft. he	eight.
Value		0.012 in.	indentation
Adhesion To Concret	e (Tensile Pu	II)	
ACI 503 R, 7 day cure		410 psi, 100% con	crete failure
Abrasion Resistance	(Taber)		
ASTM D 4060, 7 day c	ure, 1,000 cyc	cles, 1,000 g load,	
Wheel No. 17		l	_oss 0.051 g
Water Absorption			
ASTM D 570, 7 day cu	ıre,		< 0.15%
Tensile Properties			
ASTM D 638 Strengt	h - Neat Epoxy	y, 7 day cure	8,800 psi
ASTM D 638, Elongation - Neat Epoxy, 7 day cure 5%			
Flexural Properties			
ASTM D 790, Neat Ep	oxy, 7 day cur	e	
Strength			9,200 psi
Tangent Modulus of Elasticity			5.1 x 10° psi
Slant Shear Strength			
ASTM C 882, 7 day cu	ire		
Test Temperature	Value	Mode o	of Failure
90°F	4,000 psi	100% Concrete	e Failure
50°F	4,200 psi	100% Concrete	e Failure
Coefficient of Therma	al Expansion	- (°)	
Temperature Range: -	30C/30C (-22	F / 86 F)	4
ASTM D 696, 7 day cu	re,	18.0 x	: 10 ° in / in ⁰F
Flammability		0.11	
ASTM D635, 7 day cur	e,	Self	-extinguishing
Slip Resistance			
Complies with Americans with Disabilities Act (ADA), 1 itle 111, July			
1992 and UHSA Standards 29 UFR-1910. Accepted Industry			
Stanuaru, ASTIVI C 1028 Coefficient of Friction Levels range from			
0.5 to 1.0. Rating is depended on surface profile selected.			

Shelf Life

2 years in original unopened containers

Crown TD, an Epoxy Polymer Concrete Trowel Floor Overlay

Surface Preparation

All substrate surfaces must have all loose and deterioration removed to a sound surface. Concrete and other substrates must be clean, sound, and free of dust, grease, waxes, coatings, compounds and curing all contaminants. Typical removal methods include dust-free abrasive shot-blasting. Clean the substrate to the desired surface profile, until all the surface shows open pores. Follow Crown Polymer Surface Preparation Guide for best results.

Test Substrate for Cleanliness and Adhesion

Before placement of the Epoxy Polymer Concrete, check the concrete and steel substrates for soundness and cleanliness with a Tensile Pull Test (ACI 503 R) or Shear Test. 100% concrete must fail to pass either test.

Preconditioning Epoxy

When temperatures drop, polymers typically thicken and it becomes harder to flow or to spread the product. When the temperatures are warmer, they typically become thinner. To improve the flow-ability maintains product temperature before mixing at about 20°C (73°F). When the substrate temperature is 15°C (60°F) or lower, preheat each epoxy component to 90°F before mixing. Caution the pot life will be reduced by about 50%.

Mixing

Pre-mix Component "A", (when pigmented) then pour Component "B" into "A" and mix for 90 seconds with a low speed paddle attached to a drill (400-600 rpm). Pour the mixed epoxy into a clean 5 gal pail and slowly add the aggregate and mix until uniformly blended, about 4 minutes. For larger batches pour the mixed epoxy into a concrete mixer, add the aggregate into the mixer, and blend for about the same amount of time. Note: When a mixer is used, on the first batch reduce 5-10 lbs. of aggregate to allow the mixer drum surface to wet out. Be sure the mixing vessel is clean and dry.

Priming

Crown TD formula is designed to prime the surface as part of the placement process and it can normally require priming. Priming may be preferred when using a screed box for application. Problematic concrete surfaces may require priming prior to EPC placement.

Placement

Place the mixed EPC onto the surface, spread evenly with a box screed or a vibrating screed. Finish smooth with hand or power troweling methods at a compacted thickness of

³/₁₆ – ¼ in.

Limitations

- Substrate temperature must be 3°C or 5°F above measured dew point temperature.
- Minimum application temperature is 10°C (50°F). Lower curing temperature option available.
- DO NOT APPLY on WET SUBSTRATE.
- DO NOT THIN solvents could prevent proper cure.
- Aggregate must be dry when used.
- Pre-condition polymer as needed.

Caution

Before Using Read Material Safety Data Sheets.

Component "A"- Irritant

Contains epoxy resins. Prolonged contact with skin may cause irritation. Avoid contact with eyes.

Component "B" - Corrosive

Contains aliphatic/cycloaliphatic amines. Contact with skin may cause severe burns. Avoid eye contact. Product is a strong sensitizer

Component "C" - Contains silica. Avoid breathing product.

Important Information

Use of safety goggles, chemicalresistant gloves, adequate ventilation and NIOSH/OSHA approved respirator is recommended.

Clean Up

In case of spills wear suitable protective equipment, contain spill, and collect with absorbent material, place in suitable container. Ventilate area. Avoid contact. Dispose according to applicable local, state, and federal regulations.

First Aid

In case of skin contact, wash thoroughly with soap and water. For eye contact, flush immediately with plenty of water for at least 15 minutes. For respiratory problems, remove person to fresh air. Contact Physician Immediately. Wash clothing before reuse.

Consult Safety Data Sheet for More Information

FOR INDUSTRIAL USE ONLY KEEP OUT OF REACH OF CHILDREN KEEP CONTAINERS TIGHTLY CLOSED

LIMITED WARRANTY - "Crown Polymers Corp. warrants its products to be free of manufacturing defects, to be of good quality, and that they will meet Crown Polymers current published physical properties when applied in accordance with Crown Polymers written directions and tested in accordance with ACI, ASTM and Crown Polymers Standards. Product proved to be defective will be replaced. There are no other warranties by Crown Polymers Corp. of any nature whatsoever, expressed or implied, including any warranty of merchantability or fitness for a particular purpose in connection with this product. Crown Polymers Corp. shall not be liable for damages of any sort, including remote or consequential damages, resulting from any claimed breach of any warranty, whether expressed or implied, from any other cause whatsoever. Crown Polymers will not be responsible for use of this product in a manner to infringe on any patent held by others."

For the Location of Your Nearest Crown Polymers Representative

CALL NATIONWIDE TOLL-FREE 1-888 / 732-1270



USA Corporate Office & Factory Crown Polymers Corp. • PH: 847.659.0300 • Fax: 847.659.0310 • info@crownpolymers.com • www.crownpolymers.com